



U-Bent Rapid Start T8

FB29T8/TL841/EW/ALTO 15/1

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Initial lumen (Nom)	2550 lm
Design Mean Lumens	2300 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85
Operating and Electrical	
Power (Rated) (Nom)	29 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	22.44
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg
Product Data	
XUCDM.COPY.Product.Title	FB29T8/TL841/EW/ALTO 15/1
EAN/UPC - Product	046677226770
Order code	226779
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927861384102
Net Weight (Piece)	0.001 kg


Warnings and Safety

U-Bent Rapid Start T8

Dimensional drawing

Product

FB29T8/TL841/EW/ALTO 15/1



FB29T8/TL841 EW ALTO® ES

