



U-Bent Rapid Start T12

FB40DX/6 12PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Energy Saving Product	Not Applicable
Light Technical		Mercury (Hg) Content (Nom)	10.0 mg
Color Code	57	Product Data	
Luminous Flux	2,250 lm	Order product name	FB40DX/6 12PK
Color Designation	Daylight Deluxe	Full product name	FB40DX/6 12PK
Correlated Color Temperature (Nom)	6500 K	Order code	219931
Color rendering index (CRI)	90	Material Nr. (12NC)	927862005704
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	EAN/UPC - Product/Case	046677219932
Mechanical and Housing		Numerator - Packs per outer box	12
Bulb Shape	T12-6U [U-bent T 12/8 inch with 6" spacing]	EAN/UPC - Case	50046677219937

U-Bent Rapid Start T12

Dimensional drawing

Product
FB40DX/6 12PK

