



MASTER TL-D Super 80

TLDRS32W-S83ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	36000 h
Life 12-Hr Instant Start [Hrs]	30000 h
Life 3-Hr Program Start [Hrs]	30000 h
Life 3-Hr Instant Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Footnotes Fluorescent/CFL 1	Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.

Light Technical	
Color Code	TL830 [CCT of 3000K (830)]
Luminous Flux (Nom)	2600 lm
Color Designation	TL830
Design Mean Lumens	2470 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	78

Operating and Electrical	
Power (Nom)	32 W

Mechanical and Housing	
Cap-Base Information	Green Cap
Nominal Length (Inch)	48

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	27 pg/lm.h
Mercury (Hg) Content (Nom)	1.7 mg

Product Data	
Full product code	872790091775800
Order product name	TLDRS32W-S83ECO 25PK
EAN/UPC - Product	8727900917758
Order code	927869773002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927869773002
Net Weight (Piece)	134.400 g


MASTER TL-D Super 80

Warnings and Safety

Dimensional drawing

Product

TLDRS32W-S83ECO 25PK



F32T8/830

