



MASTER TL-D Super 80

TLDRS32W-S84ECO 25PK

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical	
Color Code	TL841 [CCT of 4100K (841)]
Luminous Flux	2,700 lm
Color Designation	TL841
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	32 W

Mechanical and Housing	
Bulb Shape	T-8

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	3.0 mg

Product Data	
Order product name	TLDRS32W-S84ECO 25PK
Full product name	TLDRS32W-S84ECO 25PK
Full product code	872790091777200
Order code	927869774112
Material Nr. (12NC)	927869774112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900917772
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900917789

MASTER TL-D Super 80

Dimensional drawing

Product

TLDRS32W-S84ECO 25PK

