



# TL-D Standard Colours

## TLDRS32W-CO-25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	12000 h

  

Light Technical	
Color Code	33-640
Luminous Flux (Nom)	2350 lm
Color Designation	Cool White (CW)
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	83 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	60

  

Operating and Electrical	
Power (Nom)	32 W
Lamp Current (Nom)	0.265 A
Voltage (Nom)	139 V

Controls and Dimming	
Dimmable	Yes

  

Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg

  

Product Data	
Full product code	872790091579200
Order product name	TLDRS32W-CO-25
EAN/UPC - Product	8727900915792
Order code	927870003301
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927870003301
Net Weight (Piece)	134.400 g

### Warnings and Safety

## TL-D Standard Colours

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TLDRS32W-CO-25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 32W/33-640

