



# Rapid Start T8

## F40T8/TL835 ALTO 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	TL835 [ CCT of 3500K (835)]
Initial lumen (Nom)	3775 lm
Color Designation	TL835
Design Mean Lumens	3500 lm
Correlated Color Temperature (Nom)	3500 K
Color Rendering Index (Nom)	86
Operating and Electrical	
Power (Rated) (Nom)	40 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	60
Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	50 pg/lm.h
Mercury (Hg) Content (Nom)	3.5 mg

Product Data	
Order product name	F40T8/TL835 ALTO 25PK
EAN/UPC - Product	046677368340
Order code	368340
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927870583501
Net Weight (Piece)	0.001 kg


### Warnings and Safety

## Rapid Start T8

### Dimensional drawing

#### Product

F40T8/TL835 ALTO 25PK



F40T8/835 60 ALTO ES

