



PLUS T8 High Output

F96T8/TL850/PLUS/HO/ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data


General Information		Nominal Length (Inch)	
Cap-Base	R17D [R17d (RDC)]	96	
Life 3-Hr Start [Hrs]	24000 h	Approval and Application	
Features	ALTO® Plus	Energy Saving Product	Energy Saving
Light Technical		Picogram Per Lumen Hour	24 pg/lm.h
Color Code	TL850 [CCT of 5000K (850)]	Mercury (Hg) Content (Nom)	4.4 mg
Luminous Flux (Nom)	8100 lm	Product Data	
Color Designation	TL850	Order product name	F96T8/TL850/PLUS/HO/ALTO 25/1
Design Mean Lumens	7525 lm	EAN/UPC - Product	046677236892
Correlated Color Temperature (Nom)	5000 K	Order code	236893
Color Rendering Index (Nom)	85	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	25
Power (Rated) (Nom)	86 W	Material Nr. (12NC)	927874085005
Mechanical and Housing		Net Weight (Piece)	0.001 kg
Cap-Base Information	Green Base		

PLUS T8 High Output

Dimensional drawing

Product

F96T8/TL850/PLUS/HO/ALTO 25/1



F96T8 86W/850 HO ALTO Plus

