

Lighting

PHILIPS

PLUS T8 High Output

F96T8/TL850/PLUS/HO/ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data

| General Information | |
|------------------------------------|----------------------------|
| Cap-Base | R17D [R17d (RDC)] |
| Features | ALTO [®] Plus |
| | |
| Light Technical | |
| Color Code | TL850 [CCT of 5000K (850)] |
| Luminous Flux | 8,100 lm |
| Color Designation | TL850 |
| Correlated Color Temperature (Nom) | 5000 K |
| Color rendering index (CRI) | 85 |
| | |
| Operating and Electrical | |
| Power Consumption | 86 W |
| | |
| Mechanical and Housing | |
| Bulb Shape | T-8 (T8) |
| | |

| Approval and Application | |
|---------------------------------|-------------------------------|
| Energy Saving Product | Energy Saving |
| Mercury (Hg) Content (Nom) | 4.4 mg |
| | |
| Product Data | |
| Order product name | F96T8/TL850/PLUS/HO/ALTO 25/1 |
| Full product name | F96T8/TL850/PLUS/HO/ALTO 25/1 |
| Order code | 927874085005 |
| Material Nr. (12NC) | 927874085005 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677236892 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 50046677236897 |

PLUS T8 High Output

Dimensional drawing

Product

F96T8/TL850/PLUS/HO/ALTO 25/1





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, November 6 - data subject to change