



# High Output T8

## F96T8/D/ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	FA8 [FA8]
Features	ALTO® (ALTO)

  

Light Technical	
Color Code	765 [CCT of 6500K]
Luminous Flux	4,725 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	76

  

Operating and Electrical	
Power Consumption	60 W

  

Mechanical and Housing	
Bulb Shape	T-8 (T8)

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Max)	4.4 mg

  

Product Data	
Order product name	F96T8/D/ALTO
Full product name	F96T8/D/ALTO
Order code	454124
Material Nr. (12NC)	927874776501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677454128
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677454123

# High Output T8

## Dimensional drawing

Product

F96T8/D/ALTO

