



# Retail Sales T8

## F15T8/PLANT/18 6PK

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	7500 h
Light Technical	
Color Code	7
Initial lumen (Nom)	410 lm
Color Designation	Plant and Aquarium (PLANT)
Operating and Electrical	
Power (Rated) (Nom)	15 W
Mechanical and Housing	
Cap-Base Information	Aluminium [ Aluminium Cap]
Nominal Length (Inch)	18

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Product Data	
Order product name	F15T8/PLANT/18 6PK
EAN/UPC - Product	046677392260
Order code	392266
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	927875600703
Net Weight (Piece)	59.600 g

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Retail Sales T8

### Dimensional drawing

#### Product

F15T8/PLANT/18 6PK



F15T8/7 18

