



T5 Retail Sales

F28T5/TL835 UPC 15/1

Available in a variety of lengths and lumen packages, these T5 lamps are an ideal solution for use in compact fixtures.

Warnings and Safety

- CAUTION: When changing lamps, turn off power to the fixture to avoid electric shock.
- Fluorescent lamps can shatter if broken.
- Handle with care and store in a safe place.


Product data

General Information	
Cap-Base	G5 [G5]
Features	ALTO® (ALTO)
Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	2,900 lm
Color Designation	835
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	27.9 W
Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	F28T5/TL835 ALTO UPC 15/1
Full product name	F28T5/TL835 UPC 15/1
Order code	206136
Material Nr. (12NC)	927876083503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677152376
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677206135


T5 Retail Sales

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F28T5/TL835 ALTO UPC 15/1	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - F28T5/TL835 ALTO UPC 15/1

Lifetime



Life Expectancy Diagram - F28T5/TL835 ALTO UPC 15/1



Life Expectancy Diagram - F28T5/TL835 ALTO UPC 15/1

T5 Retail Sales

Lifetime



Lumen Maintenance Diagram - F28T5/TL835 ALTO UPC 15/1

