



Preheat T12

F15T12/CW 30PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Light Technical	
Color Code	33
Luminous Flux	800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	15 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	F15T12/CW 30PK
Full product name	F15T12/CW 30PK
Order code	927882003311
Material Nr. (12NC)	927882003311
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677141493
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677141498

Preheat T12

Dimensional drawing

Product

F15T12/CW 30PK

