



Preheat T12

F20T12/WW ALTO 30PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	9000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	29
Luminous Flux (Nom)	1250 lm
Color Designation	Warm White (WW)
Design Mean Lumens	1100 lm
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	53
Operating and Electrical	
Power (Rated) (Nom)	20 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	24
Approval and Application	
Mercury (Hg) Content (Nom)	1.9 mg
Product Data	
Order product name	F20T12/WW ALTO 30PK
EAN/UPC - Product	046677273491
Order code	273490
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927883002901
Net Weight (Piece)	0.001 kg

Preheat T12

Dimensional drawing

Product

F20T12/WW ALTO 30PK



F20T12/29 24 ALTO

