



# Preheat T12

## F20T12/CW ALTO 30PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	9000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Initial lumen (Nom)	1200 lm
Color Designation	Cool White (CW)
Design Mean Lumens	1050 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	62
Operating and Electrical	
Power (Rated) (Nom)	20 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	24
Approval and Application	
Mercury (Hg) Content (Nom)	1.9 mg
Product Data	
Order product name	F20T12/CW ALTO 30PK
EAN/UPC - Product	046677273323
Order code	273326
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927883003301
Net Weight (Piece)	0.001 kg


### Warnings and Safety

## Preheat T12

### Dimensional drawing

**Product**

F20T12/CW ALTO 30PK



F20T12/33 24 ALTO

