



# Preheat T12

## F20T12/CW ALTO 30PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	33
Luminous Flux	1,200 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62
Operating and Electrical	
Power Consumption	20 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Mercury (Hg) Content (Nom)	1.9 mg
Product Data	
Order product name	F20T12/CW ALTO 30PK
Full product name	F20T12/CW ALTO 30PK
Order code	273326
Material Nr. (12NC)	927883003301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677273323
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677273328

Preheat T12

Dimensional drawing

Product
F20T12/CW ALTO 30PK

