



Rapid Start T12

F30T12/CW/RS ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

| General Information | |
|------------------------------|----------------------------------|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] |
| Life 3-Hr Start [Hrs] | 18000 h |
| Life with 3 Hour Per Day Use | 7 a |
| Features | ALTO® (ALTO) |
| System Description | RS [Rapid Start (RS)] |

| Light Technical | |
|------------------------------------|-----------------|
| Color Code | 33 |
| Luminous Flux (Nom) | 2250 lm |
| Color Designation | Cool White (CW) |
| Design Mean Lumens | 1900 lm |
| Correlated Color Temperature (Nom) | 4100 K |
| Color Rendering Index (Nom) | 62 |

| Operating and Electrical | |
|--------------------------|------|
| Power (Rated) (Nom) | 30 W |

| Mechanical and Housing | |
|------------------------|------------|
| Cap-Base Information | Green Base |
| Nominal Length (Inch) | 36 |

| Approval and Application | |
|----------------------------|----------------|
| Energy Saving Product | Not Applicable |
| Mercury (Hg) Content (Nom) | 3.5 mg |

| Product Data | |
|---------------------------------|------------------------|
| Order product name | F30T12/CW/RS ALTO 30PK |
| EAN/UPC - Product | 046677272425 |
| Order code | 272427 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 30 |
| Material Nr. (12NC) | 927886003305 |
| Net Weight (Piece) | 0.001 kg |

Rapid Start T12

Dimensional drawing

Product

F30T12/CW/RS ALTO 30PK



F30T12/33 RS 36 ALTO

