



Rapid Start T12

F30T12/CW/RS ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Warnings and Safety

· Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	18000 h
Life with 3 Hour Per Day Use	7 a
Features	ALTO® (ALTO)
System Description	Rapid Start (RS)
Light Technical	
Color Code	33
Initial lumen (Nom)	2250 lm
Color Designation	Cool White (CW)
Design Mean Lumens	1900 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	62
Operating and Electrical	
Power (Rated) (Nom)	30 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	36
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg
Product Data	
Order product name	F30T12/CW/RS ALTO 30PK
EAN/UPC - Product	046677272425
Order code	272427
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927886003305
Net Weight (Piece)	0.163 kg

Rapid Start T12

Dimensional drawing

Product

F30T12/CW/RS ALTO 30PK



F30T12/33 RS 36 ALTO

