PHILIPS

Lighting



Rapid Start T12

F30T12/CW/ALTO 15/2

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical	
Color Code	33
Luminous Flux	2,250 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Color rendering index (CRI)	62

Operating and Electrical	
Power Consumption	30 W

Mechanical and Housing	
Bulb Shape	T-12 (T12)


Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	3.5 mg

Product Data	
Order product name	F30T12/CW/ALTO 15/2
Full product name	F30T12/CW/ALTO 15/2
Order code	205591
Material Nr. (12NC)	927886003314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677205591
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677205596

Rapid Start T12

Dimensional drawing

Product
F30T12/CW/ALTO 15/2



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.