



TuffGuard Coated T12

F40T12/CWSupreme/ALTO TG

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Warnings and Safety

- All HO lamps recommended for use only in open fixtures.

Product data

General Information		Approval and Application	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Energy Saving Product	Energy Saving
Features	ALTO® (ALTO)	Mercury (Hg) Content (Nom)	4.4 mg
Light Technical		Product Data	
Luminous Flux	2,600 lm	Order product name	F40T12/CWSupreme/ALTO TG
Color Designation	Cool White Supreme	Full product name	F40T12/CWSupreme/ALTO TG
Correlated Color Temperature (Nom)	4100 K	Order code	424002
Color rendering index (CRI)	89	Material Nr. (12NC)	927887803902
Operating and Electrical		Numerator - Quantity Per Pack	1
Power Consumption	40 W	EAN/UPC - Product/Case	046677424008
Mechanical and Housing		Numerator - Packs per outer box	30
Bulb Shape	T-12 (T12)	EAN/UPC - Case	50046677424003

TuffGuard Coated T12

Dimensional drawing

Product
F40T12/CWSupreme/ALTO TG

