



TuffGuard Coated T12

F40T12/CWSupreme/ALTO TG

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life 12-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)
System Description	RS [Rapid Start (RS)]
Light Technical	
Luminous Flux (Nom)	2600 lm
Color Designation	Cool White Supreme
Design Mean Lumens	2250 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	89
Operating and Electrical	
Power (Rated) (Nom)	40 W
Mechanical and Housing	
Cap-Base Information	Green Base


Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40T12/CWSupreme/ALTO TG
EAN/UPC - Product	046677424008
Order code	424002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927887803902
Net Weight (Piece)	0.001 kg

TuffGuard Coated T12

Dimensional drawing

Product

F40T12/CWSupreme/ALTO TG



F40T12 CW Supreme ALTO

