



# High CRI T12

## F40T12/C50Supreme/ALTO 30pk

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life 12-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)

  

Light Technical	
Initial lumen (Nom)	2545 lm
Color Designation	C50 Supreme
Design Mean Lumens	2160 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	90

  

Operating and Electrical	
Power (Rated) (Nom)	40 W

  

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
-----------------------	----

  

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

  

Product Data	
XUCDM.COPY.Product.Title	F40T12/C50Supreme/ALTO 30pk
EAN/UPC - Product	046677423896
Order code	423897
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927888000213
Net Weight (Piece)	0.001 kg

### Warnings and Safety

## High CRI T12

### Dimensional drawing

#### Product

F40T12/C50Supreme/ALTO 30pk



F40T12 C50 Supreme ALTO®

