



High CRI T12

F40T12/NX/ALTO 30PK

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life 12-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)
Light Technical	
Luminous Flux (Nom)	2550 lm
Color Designation	Neutral DX
Design Mean Lumens	2220 lm
Correlated Color Temperature (Nom)	3500 K
Color Rendering Index (Nom)	88
Operating and Electrical	
Power (Rated) (Nom)	40 W
Mechanical and Housing	
Cap-Base Information	Green Base


Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40T12/NX/ALTO 30PK
EAN/UPC - Product	046677423186
Order code	423186
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927888004904
Net Weight (Piece)	0.001 kg

High CRI T12

Dimensional drawing

Product

F40T12/NX/ALTO 30PK



F40T12 Neutral DX ALTO®

