



Rapid Start T12

F40DX ALTO 30PK

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life with 3 Hour Per Day Use	7 a
Features	ALTO® (ALTO)
System Description	RS [Rapid Start (RS)]
Light Technical	
Color Code	57
Luminous Flux (Nom)	2325 lm
Color Designation	Daylight Deluxe
Design Mean Lumens	2025 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	90
Operating and Electrical	
Power (Rated) (Nom)	40 W

Mechanical and Housing	
Cap-Base Information	Green Base
Nominal Length (Inch)	48
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40DX ALTO 30PK
EAN/UPC - Product	04667273590
Order code	273599
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927888005709
Net Weight (Piece)	0.001 kg

Rapid Start T12

Dimensional drawing

Product

F40DX ALTO 30PK



F40T12/57 48 ALTO

