



Retail Sales T12

F40T12/DAYLIGHT DELUXE/ALTO 30PK

High Performance, Long Life, Environmentally-Responsible Lamps. These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)
Light Technical	
Color Code	57
Luminous Flux	2,325 lm
Color Designation	Daylight Deluxe
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	90
Operating and Electrical	
Power Consumption	40 W
Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	4.4 mg
Product Data	
Order product name	F40T12/DAYLIGHT DELUXE/ALTO 30PK
Full product name	F40T12/DAYLIGHT DELUXE/ALTO 30PK
Order code	409383
Material Nr. (12NC)	927888005733
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409388
Numerator - Packs per outer box	1
EAN/UPC - Case	50046677409383

Dimensional drawing

Product
F40T12/DAYLIGHT DELUXE/ALTO 30PK

