



High Output T12

F60T12/CW/HO/ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Base	R17D [R17d (RDC)]
Life 3-Hr Start [Hrs]	12000 h
Features	ALTO® (ALTO)

Light Technical	
Color Code	33
Initial lumen (Nom)	4945 lm
Color Designation	Cool White (CW)
Design Mean Lumens	4500 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	82

Operating and Electrical	
Power (Rated) (Nom)	75 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	60
-----------------------	----

Approval and Application	
Mercury (Hg) Content (Nom)	6.8 mg

Product Data	
Order product name	F60T12 CW HO ALTO
EAN/UPC - Product	04667234317
Order code	234310
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927891303301
Net Weight (Piece)	0.001 kg

Warnings and Safety

High Output T12

Dimensional drawing

Product

F60T12 CW HO ALTO

F60T12 75W/33 HO ALTO®

