



Slimline T12

Slimline F72T12/D ALTO 15PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

General Information	
Base	FA8 [FA8]
Life 3-Hr Start [Hrs]	12000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	54
Initial lumen (Nom)	3800 lm
Color Designation	Daylight
Design Mean Lumens	3350 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	79
Operating and Electrical	
Power (Rated) (Nom)	56 W
Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	72
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg

Product Data	
Order product name	Slimline F72T12/D ALTO 15PK
EAN/UPC - Product	046677369859
Order code	369850
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927893005403
Net Weight (Piece)	0.001 kg

Warnings and Safety


• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Slimline T12

Dimensional drawing

Product

Slimline F72T12/D ALTO 15PK



F72T12 56W/54 ALTO

