



T5 TuffGuard Coated

F54T5/841/HO/ALTO TG 40PK

When you select Philips TuffGuard™ Fluorescent lamp with ALTO® lamp technology, you are reducing the impact on the environment, while the coating helps to protect your customers, employees, and reputation. Philips TuffGuard™ fluorescent lamps meet sustainability requirements because they reduce the impact on the environment with low mercury, energy efficiency and long life. The patented green endcaps mean you're using ALTO low-mercury technology. The 16 mils thick coating on TuffGuard™ fluorescent lamps forms a protective seal from end to end and is guaranteed to last the average rated life of the lamp under specific conditions

Product data

General Information		Operating and Electrical	
Base	G5 [G5]	Luminous Efficacy (rated) (Nom)	83 lm/W
Life to 50% Failures Preheat (Nom)	30000 h	Color Rendering Index (Max)	85
Features	HO Alto® [High Output Alto]	Color Rendering Index (Min)	80
System Description	High Output (HO)	Color Rendering Index (Nom)	82
LSF Preheat 2000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF Preheat 4000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF Preheat 6000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF Preheat 8000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 16000 h Rated	97 %	LLMF 12000 h Rated	92 %
LSF Preheat 20000 h Rated	84 %	LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical		Temperature	
Color Code	841 [CCT of 4100K]	Power (Rated) (Nom)	54 W
Initial lumen (Nom)	5000 lm	Lamp Current (Nom)	0.455 A
Luminous Flux (Rated) (Nom)	4500 lm		
Color Designation	Cool White (CW)	Design Temperature (Nom)	35 °C
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	93 lm/W		
Correlated Color Temperature (Nom)	4100 K		

T5 TuffGuard Coated

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green [Green Cap]
----------------------	--------------------

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg


Product Data

Order product name	F54T5/841/HO/ALTO TG 40PK
--------------------	---------------------------

EAN/UPC - Product	046677162986
Order code	162982
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927893184102
Net Weight (Piece)	0.001 kg
ILCOS Code	FDH-54/40/1B-L/P-G5-16/1150

Warnings and Safety

Dimensional drawing




Product


F54T5/841/HO/ALTO TG 40PK

TL5 HO F54T5/841 HO Alto TG

Photometric data




LDPB_TL5-HO8_840-Spectral power distribution B/W




LDPO_TL5-HO8_840-Spectral power distribution Colour

T5 TuffGuard Coated

Lifetime



LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

