



# High Output T12

## F72T12/D/HO ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

### Product data

General Information	
Cap-Base	R17D [R17d (RDC)]
Features	ALTO® (ALTO)

Light Technical	
Color Code	54
Luminous Flux	5,600 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	79

Operating and Electrical	
Power Consumption	85 W

Mechanical and Housing	
Bulb Shape	T-12 (T12)

Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg


Product Data	
Order product name	F72T12/D/HO ALTO 15PK
Full product name	F72T12/D/HO ALTO 15PK
Order code	366534
Material Nr. (12NC)	927893205402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677366537
Numerator - Packs per outer box	15
EAN/UPC - Case	50046677366532

# High Output T12

## Dimensional drawing

### Product

F72T12/D/HO ALTO 15PK



T12 Recessed Double Contact

