



TUV PL-S

TUV PL-S 9W/2P 1CT/6X10BOX

TUV PL-S lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-S lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

产品数据


一般信息	
底盖	G23 [G23]
有效寿命 (标称)	9,000 小时
灯技术	
颜色代码	TUV
颜色名称	- [未指定]
有效寿命下的衰减	20 %
操作和电气	
功耗	8.6 W
灯具电流 (标称)	0.17 A
电压 (标称)	60 V

电压 (标称)	60 V
机械和外壳	
灯泡外形	2XT12
审批和申请	
汞 (Hg) 含量 (标称)	3.0 mg
UV	
100 小时下的紫外线 C 辐射	2.5 W
产品数据	
订单产品名称	TUV PL-S 9W/2P 1CT/6X10BOX
完整的产品名称	TUV PL-S 9W/2P 1CT/6X10BOX

完整产品代码	871150061824580
订购代码	927901704007
材料编号 (12NC)	927901704007
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500618245


计算器 - 每个外包装箱中的包数	60
EAN/UPC - 案例	8711500618269

二维绘图



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-S 9W/2P 1CT/6X10BOX	13 mm	28 mm	129 mm	144.5 mm	167 mm

光度数据



Spectral Power Distribution Colour - TUV PL-S 9W/2P 1CT/6X10BOX

