



TUV PL-S

TUV PL-S 11W/2P 1CT/6X10BOX

TUV PL-S lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-S lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Product data

General Information	
Base	G23 [G23]
Main Application	Disinfection
Useful Life (Nom)	9000 h
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	20 %
Operating and Electrical	
Power (Rated) (Nom)	11 W
Lamp Current (Nom)	0.16 A
Voltage (Nom)	89 V
Mechanical and Housing	
Cap-Base Information	2 Pins (2P)

Warnings and Safety

Approval and Application	
Mercury (Hg) Content (Nom)	3.0 mg
UV	
UV-C Radiation at 100 hr	3.2 W
Product Data	
Order product name	TUV PL-S 11W/2P 1CT/6X10BOX
EAN/UPC - Product	8711500624888
Order code	285650
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	60
Material Nr. (12NC)	927902304007
Net Weight (Piece)	53.230 g

TUV PL-S

Dimensional drawing

Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-S 11W/2P 1CT/ 6X10BOX	13 mm	28 mm	198 mm	213.3 mm	236.3 mm

TUV 11W PL-S

Photometric data

