



MASTER PL-L 4 Pin 4-針腳型

MASTER PL-L 18W/865/4P 1CT/25

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 2 個平行螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	2G11
通量測量參考	Sphere
壽命 (故障率 50 %) (標稱)	15,000 h
照明技術	
色碼	865 [CCT of 6500K]
光通量	1,170 lm
色彩名稱	冷日光色
色度坐標 X (標稱)	0.313
色度坐標 Y (Nom)	0.337
相關色彩溫度 (規範)	6500 K
光效 (額定) (標準)	65 lm/W
演色性指數 (CRI)	80


運轉與電力	
耗電量	18.0 W
燈具電流 (標稱)	0.375 A
控制與調光	
可調光	是
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	2 mg
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	18 kWh
EPREL 註冊碼	423264
產品資料	
下訂產品名稱	MASTER PL-L 18W/865/4P 1CT/25

MASTER PL-L 4 Pin 4-針腳型

完整產品名稱	MASTER PL-L 18W/865/4P 1CT/25
完整產品代碼	871150063514340
訂單代碼	927903086572
材質 Nr. (12NC)	927903086572
分子 - 每個包裝的數量	1


EAN/UPC - 產品/案例	8711500635143
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500635150

二维绘图



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

光度数据



Spectral Power Distribution Colour - MASTER PL-L 18W/865/4P 1CT/25

