



MASTER PL-L 4 Pin

MASTER PL-L 18W/865/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	2G11	Correlated Color Temperature (Nom)	6500 K
Flux measurement reference	Sphere	Luminous Efficacy (rated) (Nom)	65 lm/W
Life to 50% Failures (Nom)	15,000 hour(s)	Color rendering index (CRI)	80
Light Technical		Controls and Dimming	
Color Code	865 [CCT of 6500K]	Power Consumption	18.0 W
Luminous Flux	1,170 lm	Lamp Current (Nom)	0.375 A
Color Designation	Cool Daylight	Dimmable	Yes
Chromaticity Coordinate X (Nom)	0.313		
Chromaticity Coordinate Y (Nom)	0.337		

MASTER PL-L 4 Pin

Approval and Application


Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	18 kWh
EPREL Registration Number	423264

Product Data

Order product name	MASTER PL-L 18W/865/4P 1CT/25
Full product name	MASTER PL-L 18W/865/4P 1CT/25


Full product code	871150063514340
Order code	927903086572
Material Nr. (12NC)	927903086572
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635143
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500635150

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/865/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 18W/865/4P 1CT/25

