



MASTER PL-L 4 Pin

MASTER PL-L 24W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | 2G11 [2G11] |
| Flux measurement reference | Sphere |
| Life to 50% Failures (Nom) | 15,000 hour(s) |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 1,800 lm |
| Color Designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 75 lm/W |
| Color rendering index (CRI) | 80 |
| Operating and Electrical | |
| Power Consumption | 24.2 W |


| Lamp Current (Nom) | 0.345 A |
|-------------------------------|-------------------------------|
| Controls and Dimming | |
| Dimmable | Yes |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) Content (Max) | 2 mg |
| Mercury (Hg) Content (Nom) | 2.0 mg |
| Energy Consumption kWh/1000 h | 25 kWh |
| EPREL Registration Number | 423267 |
| Product Data | |
| Order product name | MASTER PL-L 24W/840/4P 1CT/25 |
| Full product name | MASTER PL-L 24W/840/4P 1CT/25 |
| Full product code | 871150070672040 |
| Order code | 927903208470 |

MASTER PL-L 4 Pin

| | |
|-------------------------------|---------------|
| Material Nr. (12NC) | 927903208470 |
| Local order code | PLL24W8404P |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500706720 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 8711500710826 |

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|-------------------------------|---------|----------|----------|---------|----------|
| MASTER PL-L 24W/840/4P 1CT/25 | 39.0 mm | 18.0 mm | 289.2 mm | 315 mm | 321.6 mm |

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 24W/840/4P 1CT/25

