



TUV PL-L

TUV PL-L 36W 25PK

TUV PL-L lamps are compact UVC (germicidal) lamps used in professional water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		
Cap-Base	2G11 [2G11]	
Useful Life (Nom)	9,000 hour(s)	
Light Technical		
Color Code	TUV	
Color Designation	- [Not Specified]	
Depreciation at Useful Lifetime	20 %	
Operating and Electrical		
Power Consumption	36 W	

Lamp Current (Nom)	0.435 A
Voltage (Nom)	106 V
Voltage (Nom)	106 V
Mechanical and Housing	
Bulb Shape	2xT16
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg


Datasheet, 2023, September 19 data subject to change

TUV PL-L

UV	
UV-C Radiation at 100 hr	12.2 W
Product Data	
Order product name	TUV PL-L 36W/4P 1CT/25
ull product name	TUV PL-L 36W 25PK
Full product code	871150062878740
Order code	265850

Material Nr. (12NC)	927903404007	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500628787	
Numerator - Packs per outer box	25	
EAN/UPC - Case	8711500628794	


Dimensional drawing



 Product
 D1 (max)
 D (max)
 A (max)
 B (max)
 C (max)

 TUV PL-L 36W/4P 1CT/25
 3/4 inch
 1-1/2 inch
 15-3/16 inch
 16-3/16 inch
 16-3/8 inch

Photometric data



Spectral Power Distribution Colour - TUV PL-L 36W/4P 1CT/25



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.