



MASTER PL-L 4 Pin



MASTER PL-L 36W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | 2G11 |
| Flux measurement reference | Sphere |
| Life to 50% Failures (Nom) | 15,000 hour(s) |
| | |
| Light Technical | |
| Color Code | 840 [CCT of 4000K] |
| Luminous Flux | 2,850 lm |
| Color Designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 81 lm/W |
| Color rendering index (CRI) | 80 |
| | |
| Operating and Electrical | |
| Power Consumption | 36.3 W |

| Lamp Current (Nom) | 0.435 A |
|-------------------------------|-------------------------------|
| | |
| Controls and Dimming | |
| Dimmable | Yes |
| | |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) Content (Max) | 2 mg |
| Mercury (Hg) Content (Nom) | 2.0 mg |
| Energy Consumption kWh/1000 h | 37 kWh |
| EPREL Registration Number | 423271 |
| | |
| Product Data | |
| Order product name | MASTER PL-L 36W/840/4P 1CT/25 |
| Full product name | MASTER PL-L 36W/840/4P 1CT/25 |
| Full product code | 871150070675140 |
| Order code | 70675140 |

MASTER PL-L 4 Pin

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 927903408470 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500706751 |
| Numerator - Packs per outer box | 25 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8711500711014 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|-------------------------------|---------|----------|----------|---------|----------|
| MASTER PL-L 36W/840/4P 1CT/25 | 39.0 mm | 18.0 mm | 384.2 mm | 410 mm | 416.6 mm |

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/840/4P 1CT/25

