



MASTER PL-L 4 Pin



MASTER PL-L 36W/865/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G11 [2G11]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	865 [CCT of 6500K]
Luminous Flux	2,800 lm
Colour designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Colour Temperature	6500 K
Luminous efficacy (rated) (nom.)	80 lm/W
Colour rendering index (CRI)	80
Operating and Electrical	
Power Consumption	36.3 W


Lamp current (nom.)	0.435 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	2 mg
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	37 kWh
EPREL registration number	423272
Product Data	
Order product name	MASTER PL-L 36W/865/4P 1CT/25
Full product name	MASTER PL-L 36W/865/4P 1CT/25
Full EOC	871150063520440
Order code	63520440

MASTER PL-L 4 Pin

Material no. (12 NC)	927903486570
Local order code	36PLL865
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500635204


Numerator – packs per outer box	25
EAN/UPC – Case	8711500635211

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 36W/865/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/865/4P 1CT/25

