

# **MASTER PL-L 4 Pin**

# MASTER PL-L 36W/865/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

## **Warnings and Safety**

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- · Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


#### **Product data**

General Information	
Cap-Base	2G11 [2G11]
Nominal lifetime	15,000 hour(s)
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	2,900 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.435 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	40 kWh
Product Data	
Order product name	MASTER PL-L 36W/865/4P 1CT/25
Full product name	MASTER PL-L 36W/865/4P 1CT/25
Full product code	871150063520441
Order code	927903486572
Material Nr. (12NC)	927903486572
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500635204
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500635211

Datasheet, 2023, April 14 data subject to change


# Dimensional drawing



 Product
 D (max)
 D1 (max)
 A (max)
 B (max)
 C (max)

 MASTER PL-L 36W/865/4P 1CT/25
 39.0 mm
 18.0 mm
 384.2 mm
 410 mm
 416.6 mm

### Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/865/4P 1CT/25



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.