



MASTER PL-C 2 Pin

MASTER PL-C 13W/827/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24d-1
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	925 lm
Color Designation	Incandescent White
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	69 lm/W


Color rendering index (CRI)	83
Operating and Electrical	
Power Consumption	13.4 W
Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	No

MASTER PL-C 2 Pin

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	17 kWh
Product Data	
Order product name	MASTER PL-C 13W/827/2P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/827/2P 1CT/5X10BOX
Full product code	871150062081100


Order code	927904882701
Material Nr. (12NC)	927904882701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500620811
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500621030

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/827/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	139.4 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/827/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/827/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 13W/827/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 13W/827/2P 1CT/5X10BOX

