



# MASTER PL-C 2 Pin

## MASTER PL-C 18W/840/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

### Warnings and Safety

- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	G24d-2	82	
Life to 50% Failures (Nom)	10,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	17.9 W
Luminous Flux	1,200 lm	Lamp Current (Nom)	0.230 A
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	67 lm/W		

MASTER PL-C 2 Pin

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Order product name	MASTER PL-C 18W/840/2P 1CT/5X10BOX
Full product name	MASTER PL-C 18W/840/2P 1CT/5X10BOX
Full product code	871150064272100


Order code	927905784001
Material Nr. (12NC)	927905784001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500642721
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500630001

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/840/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	150.4 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-C 18W/840/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 18W/840/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 18W/840/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 18W/840/2P 1CT/5X10BOX

