



MASTER PL-C 2 Pin

MASTER PL-C 26W/830/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Product data

General Information	
Cap base	G24D-3 [G24d-3]
Life to 10% failures (nom.)	6500 h
Life to 50% failures (nom.)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %
Light Technical	
Colour Code	830 [CCT of 3,000 K]
Lamp Luminous Flux 25°C EL (Nom)	1800 lm
Lamp Luminous Flux (Nom)	1800 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Nom)	68 lm/W
Colour Rendering Index, horiz (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	26.5 W

Lamp current (nom.)	0.335 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	no
Mechanical and Housing	
Cap base information	2P
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh
Product Data	
Full product code	871150027090000
Order product name	MASTER PL-C 26W/830/2P 1CT/5X10BOX
EAN/UPC – product	8711500270900
Order code	927906183001
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	927906183001
Net weight (piece)	64.300 g


MASTER PL-C 2 Pin

ILCOS Code

FSQ-26/30/1B-I-G24d-3

Warnings and Safety


Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm

PL-C 26W/830/2P

Photometric data





Lightcolour /830



Lightcolour /830


Lifetime



LDLE_PLC2P_0001-Life expectancy diagram

MASTER PL-C 2 Pin

Lifetime



LDLM_PLC2P_0001-Lumen maintenance diagram

