



MASTER PL-C 2 Pin

MASTER PL-C 26W/865/2P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Use only with electromagnetic control gear
- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	G24d-3	80	
Life to 50% Failures (Nom)	10,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Power Consumption	26.5 W
Luminous Flux	1,740 lm	Lamp Current (Nom)	0.335 A
Color Designation	Cool Daylight	Controls and Dimming	
Correlated Color Temperature (Nom)	6500 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	66 lm/W		

MASTER PL-C 2 Pin

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	32 kWh
Product Data	
Order product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
Full product name	MASTER PL-C 26W/865/2P 1CT/5X10BOX
Full product code	871869960680000


Order code	927906186565
Material Nr. (12NC)	927906186565
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699606800
Numerator - Packs per outer box	50
EAN/UPC - Case	8718699606824

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/865/2P 1CT/ 5X10BOX	27.1 mm	27.1 mm	130.5 mm	149.0 mm	171.4 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-C 26W/865/2P 1CT/5X10BOX

MASTER PL-C 2 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-C 26W/865/2P 1CT/5X10BOX

