



PL-T Triple 4-Pin Base Energy Advantage

PL-T 32W/830/XEW/A/4P/ALTO 27W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

General Information		Operating and Electrical	
Base	GX24Q-3 [GX24q-3]	Power (Rated) (Nom)	28 W
Life to 50% Failures Preheat (Nom)	16000 h	Lamp Current (Nom)	0.320 A
Features	ALTO® (ALTO)		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Initial lumen (Nom)	1900 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Lumen Maintenance 2000 h (Nom)	92 %	Cap-Base Information	4P
Lumen Maintenance 5000 h (Nom)	87 %		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	70 lm/W	Mercury (Hg) Content (Nom)	1.4 mg
Color Rendering Index (Nom)	>80		
		Product Data	
		Order product name	PL-T 32W/830/XEW/A/4P/ALTO 27W
		EAN/UPC - Product	046677220211

PL-T Triple 4-Pin Base Energy Advantage

Order code	220210
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927906983020

Net Weight (Piece)	70.000 g
--------------------	----------

Warnings and Safety

Dimensional drawing

Product	D (max)	B (max)	C (max)
PL-T 32W/830/XEW/A/4P/ALTO 27W	41.0 mm	123.0 mm	138.7 mm

PL-T XEW 32W/830/4P ALTO 27W

Photometric data

Φ 55 mm

