



MASTER PL-C 4 Pin

MASTER PL-C 13W/830/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24q-1
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	900 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	72 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	13.0 W


Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	MASTER PL-C 13W/830/4P 1CT/5X10BOX
Full product name	MASTER PL-C 13W/830/4P 1CT/5X10BOX
Full product code	871150062331700

MASTER PL-C 4 Pin

Order code	927907183001
Material Nr. (12NC)	927907183001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500623317


Numerator - Packs per outer box	50
EAN/UPC - Case	8711500715722

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 13W/830/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	97.5 mm	117.0 mm	131.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 13W/830/4P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 13W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 13W/830/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 13W/830/4P 1CT/5X10BOX

