



MASTER PL-C 4 Pin

MASTER PL-C 18W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Product data


General Information	
Cap base	G24Q-2 [G24q-2]
Life to 50% failures preheat (nom.)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Lamp Luminous Flux 25°C EL (Nom)	1200 lm
Lamp Luminous Flux (Nom)	1200 lm
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	67 lm/W
Colour Rendering Index, horiz (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.230 A

Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Full product code	871150062334870
Order product name	MASTER PL-C 18W/840/4P 1CT/5X10BOX
EAN/UPC – product	8711500623348
Order code	62334870
Numerator – quantity per pack	1
Numerator – packs per outer box	50
Material no. (12NC)	927907284040
Net weight (piece)	55.300 g
ILCOS Code	FSQ-18/40/1B-E-G24q=2

MASTER PL-C 4 Pin

Warnings and Safety


Dimensional drawing




PL-C 18W/840/4P

Product
MASTER PL-C 18W/840/4P 1CT/5X10BOX

Photometric data




Lightcolour /840




Lightcolour /840

Lifetime



LDLE_PLC4P_0001-Life expectancy diagram



LDLE_PLC4P_0002-Life expectancy diagram

MASTER PL-C 4 Pin

Lifetime



LDLM_PLC4P_0001-Lumen maintenance diagram

