

MASTER PL-C 4 Pin

MASTER PL-C 18W/865/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G24q-2

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,120 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	62.3 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	18.0 W
Lamp Current (Nom)	0.230 A

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	20 kWh

MASTER PL-C 4 Pin

Product Data	
Order product name	MASTER PL-C 18W/865/4P 1CT/5X10BOX
Full product name	MASTER PL-C 18W/865/4P 1CT/5X10BOX
Full product code	871150027704600
Order code	927907286501
Material Nr. (12NC)	927907286501


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500277046
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500277121

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/865/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 18W/865/4P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 18W/865/4P 1CT/5X10BOX

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.