



# PL-C Cluster 4-Pin Base

## PL-C 26W/41/4P/ALTO 10PK


Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information		Approval and Application	
Cap-Base	G24q-3	Mercury (Hg) Content (Nom)	1.4 mg
		Energy Consumption kWh/1000 h	29 kWh
Light Technical		Product Data	
Color Code	841 [CCT of 4100K]	Order product name	PL-C 26W/41/4P/ALTO 10PK
Luminous Flux	1,800 lm	Full product name	PL-C 26W/41/4P/ALTO 10PK
Color Designation	Cool White (CW)	Order code	927907384030
Correlated Color Temperature (Nom)	4100 K	Material Nr. (12NC)	927907384030
Luminous Efficacy (rated) (Nom)	67 lm/W	Numerator - Quantity Per Pack	1
Color rendering index (CRI)	82	EAN/UPC - Product/Case	046677111779
Operating and Electrical		Numerator - Packs per outer box	10
Power Consumption	26.0 W	EAN/UPC - Case	60046677111771
Lamp Current (Nom)	0.335 A		
Controls and Dimming			
Dimmable	Yes		


# PL-C Cluster 4-Pin Base

## Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-C 26W/41/4P/ALTO 10PK	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

## Photometric data




Spectral Power Distribution Colour - PL-C 26W/41/4P/ALTO 10PK

## Lifetime




Life Expectancy Diagram - PL-C 26W/41/4P/ALTO 10PK



Life Expectancy Diagram - PL-C 26W/41/4P/ALTO 10PK

## PL-C Cluster 4-Pin Base

### Lifetime



Lumen Maintenance Diagram - PL-C 26W/41/4P/ALTO 10PK

