



PL-L Long 4-Pin Base

PL-L 40W/841/4P/RS/IS

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information	
Cap-Base	2G11 [2G11]
Life to 50% Failures (Nom)	10000 h
System Description	RS [Rapid Start (RS)]
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux (Nom)	3500 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	91 %
Lumen Maintenance 2000 h (Nom)	94 %
Lumen Maintenance 5000 h (Nom)	92 %
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color Rendering Index (Nom)	82
Operating and Electrical	
Power (Rated) (Nom)	36.3 W
Lamp Current (Nom)	0.320 A

Voltage (Nom)	126 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Product Data	
Order product name	PL-L 40W/841/4P/RS/IS
EAN/UPC - Product	046677111809
Order code	927908008429
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927908008429
Net Weight (Piece)	140.000 g
ILCOS Code	FSD-40/40/1B-L/P-2G11

PL-L Long 4-Pin Base


Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/841/4P/RS/IS	39 mm	18 mm	540 mm	565 mm	571.6 mm

PL-L 40W/840/4P RS

Photometric data



Lightcolor /840



Lightcolor /840

