



MASTER PL-L 4 Pin

MASTER PL-L 55W/840/4P 1CT/25

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes

Product data

General Information	
Cap base	2G11 [2G11]
Life to 50% failures preheat (nom.)	20000 h
System description	High Frequency [High Frequency (HF)]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Colour Code	840 [CCT of 4,000 K]
Lamp Luminous Flux 25°C EL (Nom)	4800 lm
Lamp Luminous Flux (Nom)	4800 lm
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	87 lm/W
Colour Rendering Index,horiz (Nom)	82
LLMF 2000 h Rated	95 %
LLMF 4000 h Rated	94 %
LLMF 6000 h Rated	93 %
LLMF 8000 h Rated	92 %
LLMF 12000 h Rated	91 %
LLMF 16000 h Rated	90 %

LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	55.0 W
Lamp current (nom.)	0.525 A
Temperature	
Design temperature (nom.)	30 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg
Energy Consumption kWh/1000 h	61 kWh
Product Data	
Full product code	871150061542840
Order product name	MASTER PL-L 55W/840/4P 1CT/25
EAN/UPC – product	8711500615428
Order code	61542840


MASTER PL-L 4 Pin

Local Code	9279-087-08470
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927908708470

Net weight (piece)	134.000 g
ILCOS Code	FSDH-55/40/1B-L/P-2G11

Warnings and Safety


Dimensional drawing



PL-L 55W/840/4P HF

Product	MASTER PL-L 55W/840/4P 1CT/25
---------	-------------------------------

Photometric data



Lightcolour /840

Lightcolour /840

