



MASTER PL-L 4 Pin

MASTER PL-L 55W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)		87 lm/W
Cap-Base	2G11 [2G11]	Color rendering index (CRI)	80	
Flux measurement reference	Sphere	Operating and Electrical		
Light Technical		Power Consumption	55.3 W	
Color Code	840 [CCT of 4000K]	Lamp Current (Nom)	0.525 A	
Luminous Flux	4,700 lm	Controls and Dimming		
Color Designation	Cool White (CW)	Dimmable	Yes	
Chromaticity Coordinate X (Nom)	0.38			
Chromaticity Coordinate Y (Nom)	0.38			
Correlated Color Temperature (Nom)	4000 K			

MASTER PL-L 4 Pin

Approval and Application


Energy Efficiency Class	G
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	56 kWh
EPREL Registration Number	423314

Product Data

Order product name	MASTER PL-L 55W/840/4P 1CT/25
Full product name	MASTER PL-L 55W/840/4P 1CT/25


Full product code	871150061542840
Order code	927908708470
Material Nr. (12NC)	927908708470
Local order code	9279-087-08470
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500615428
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500615527

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 55W/840/4P 1CT/25

