



MASTER PL-L Xtra 4 Pin

MASTER PL-L XTRA 55W/840/4P 1CT/25

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap base	2G11 [2G11]
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	4,800 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	87 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	55.0 W
Lamp current (nom.)	0.525 A

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) content (nom.)	3.0 mg
Energy consumption kWh/1,000 hours	61 kWh
Product Data	
Order product name	MASTER PL-L Xtra 55W/840/4P 1CT/25
Full product name	MASTER PL-L XTRA 55W/840/4P 1CT/25
Full EOC	871150089764040
Order code	89764040
Material no. (12 NC)	927908884014
Local order code	55PLL840XTRA
SAP numerator – quantity per pack	1

MASTER PL-L Xtra 4 Pin


EAN/UPC — Product/Case	8711500897640
Numerator – packs per outer box	25
EAN/UPC - Case	8711500897657

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L Xtra 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L Xtra 55W/840/4P 1CT/25

